

Nano N2-Series GEN2 12130 Nitrogen Generator

- * 95 to 99.5% purity
- * The perfect economical “plug & play” nitrogen supply
- * Safe & Reliable (no hassle with gas cylinders or liquid nitrogen)
- * Installation in spaces too small for twin tower systems
- * Lower air consumption and refined controls provide energy efficiency
- * Reduces carbon footprint by eliminating gas delivery to your facility
- * 2 years warranty



Voltage	V	100 to 240v AC	Optional 24V DC
Frequency	Hz	50 or 60hz	
Operating pressure	barg	Min 6 – Max 10 ²⁾	
Recommended operating temperature	Celcius	5 - 50	
Max inlet particulate	Micron	0.1 Micron	
Recommended inlet dew point	°C	-40 PDP ³⁾	
Max inlet oil content	ppm	0.01 ⁴⁾	
Dimensions HxWxD	MM	1811 x 399 x 2428	
Weight	Kg	1.137	

Rated outlet flow ¹⁾	Nitrogen purity at the outlet (max Oxygen content)						
	99.5% (0.5%)	99% (1%)	98% (2%)	97% (3%)	96% (4%)	95% (5%)	
Nm ³ /hour	100.9	112.1	141	161.8	184.2	200.3	

pressure correction factors ⁵⁾					
inlet air pressure (barg)	6	7	8	9	10
correction factor	0.88	1.00	1.10	1.20	1.20

temperature correction factors ⁵⁾										
inlet air temperature (°C)	5	10	15	20	25	30	35	40	45	50
correction factor	0.80	0.90	0.94	1.00	1.00	0.98	0.95	0.90	0.85	0.72

- 1) At 7 barg inlet pressure and 20-25 °C inlet temperature. For outlet flow at all other conditions, refer to the correction factors above or contact our sales department at info@tech-air.nl
- 2) For pressures above 10 barg contact our sales department at info@tech-air.nl
- 3) Requires an upstream dryer. Contact us for selecting the optimum dryer for your application
- 4) Including oil vapour
- 5) To be used as a rough guide only. Contact us for sizing assistance

Connections are 1"BSPP inlet and to buffer vessel. ½" BSPP outlet and from buffer vessel