

## Nano N2-Series GEN2 6130 Nitrogen Generator

- \* 95 to 99.5% purity
- \* The perfect economical “plug & play” nitrogen supply
- \* Safe & Reliable (no hassle with gas cylinders or liquid nitrogen)
- \* Installation in spaces too small for twin tower systems
- \* Lower air consumption and refined controls provide energy efficiency
- \* Reduces carbon footprint by eliminating gas delivery to your facility
- \* 2 years warranty



Voltage	V	100 to 240v AC	Optional 24V DC
Frequency	Hz	50 or 60hz	
Operating pressure	barg	Min 6 – Max 10 <sup>2)</sup>	
Recommended operating temperature	Celcius	5 - 50	
Max inlet particulate	Micron	0.1 Micron	
Recommended inlet dew point	°C	-40 PDP <sup>3)</sup>	
Max inlet oil content	ppm	0.01 <sup>4)</sup>	
Dimensions HxWxD	MM	1811 x 399 x 1420	
Weight	Kg	675	

Rated outlet flow <sup>1)</sup>	Nitrogen purity at the outlet (max Oxygen content)						
	99.5% (0.5%)	99% (1%)	98% (2%)	97% (3%)	96% (4%)	95% (5%)	
Nm <sup>3</sup> /hour	56.7	63.0	79.2	90.9	103.5	112.5	

pressure correction factors <sup>5)</sup>					
inlet air pressure (barg)	6	7	8	9	10
correction factor	0.88	1.00	1.10	1.20	1.20

temperature correction factors <sup>5)</sup>										
inlet air temperature (°C)	5	10	15	20	25	30	35	40	45	50
correction factor	0.80	0.90	0.94	1.00	1.00	0.98	0.95	0.90	0.85	0.72

- 1) At 7 barg inlet pressure and 20-25 °C inlet temperature. For outlet flow at all other conditions, refer to the correction factors above or contact our sales department at [info@tech-air.nl](mailto:info@tech-air.nl)
- 2) For pressures above 10 barg contact our sales department at [info@tech-air.nl](mailto:info@tech-air.nl)
- 3) Requires an upstream dryer. Contact us for selecting the optimum dryer for your application
- 4) Including oil vapour
- 5) To be used as a rough guide only. Contact us for sizing assistance

Connections are 1"BSPP inlet and to buffer vessel. ½" BSPP outlet and from buffer vessel